



## PowerPRO

PowerPRO electrophoresis power supplies with category leading specifications and value.

Each power supply has a 2.4" LCD display showing the available options as well as current running conditions. Constant voltage, current and power options are available as well as pre-programmed or customer programmed conditions allowing users to save and repeat their experiments for exceptional reproducibility. The 5 power outlet pairs mean less power supplies are needed for the same number of tanks, saving cost and time when running multiple tanks simultaneously.



## Electrophoresis Power Supplies

Combining excellent specification, performance, reliability with unparalleled value.

### 3AMP

- Perfect for vertical Electrophoresis using omniPAGE Maxi.
- Blotting using omniBLOT and semidry blotters.

At 300V, 3000mA, 300W, the powerPRO 3AMP is designed for virtually all high current electrophoresis applications.

The powerPRO 3AMP's higher current output capability is perfect for electroblotting units with high-intensity plate electrodes, particularly Thistle Scientific omniBLOT maxi, VS20 WAVE and semi dry blotting systems. Electrotransfers may be performed as timed runs in constant or programmable mode to prevent overheating and buffer depletion. A run time extendable to a maximum 999 minutes in constant mode is also useful for overnight transfers undertaken at constant low current in wire electrode systems. The powerPRO 3AMP shares the built-in protocol and constant parameter features of the other powerPRO models.

### 300V

- Routine horizontal electrophoresis using multiSUB Mini, Midi and Choice.
- Vertical Electrophoresis using omniPAGE Mini.

The powerPRO 300 is a versatile multifunction power supply suitable for a wide range of electrophoresis applications.

At 300V, 700mA and 150W the powerPRO 300 has nearly twice the current and power of the market leading equivalent unit. Perfectly suited for use with Thistle Scientific's multiSUB range of horizontal electrophoresis systems and omniPAGE Mini vertical electrophoresis systems. The powerPRO 300 even has built in pre-set protocols from running each of Thistle Scientific's electrophoresis systems, and allows users to create and save protocols for their own systems.

### 500V

- Routine horizontal electrophoresis using multiSUB Mini, Midi and Choice.
- Vertical Electrophoresis using omniPAGE Mini.
- Thistle Scientific DGGE.
- Vertical Electrophoresis using omniPAGE Maxi.

With a maximum 500V, 800mA and 300W voltage, current and power output, the powerPRO 500 is an excellent general-purpose power supply that fits the broadest range of electrophoresis applications.

It can run as many as five units under a constant or programmable setting and has the capacity to store up to 30 programmed files, each with 6 steps. This makes the powerPRO 500 perfect for techniques that benefit from subtle and gradual stepwise changes in the electrical parameters as the run progresses, such as DGGE and large format vertical PAGE using Thistle Scientific VS20-DGGE and WAVE systems. The powerPRO 500 even has built in preset protocols from running each of Thistle Scientific's electrophoresis systems, and allows users to create and save protocols for their own systems.

## Technical Specifications

| Cat. No.              | PowerPRO300   | PowerPRO500                                    | PowerPRO500      |
|-----------------------|---------------|------------------------------------------------|------------------|
| Display               | 2.4" TFT      | 2.4" TFT                                       | 2.4" TFT         |
| Output Voltage / Inc. | 5-300V / 1V   | 5-500V / 1V                                    | 5-300V / 1V      |
| Output Current / Inc. | 1-700mA / 1mA | 1-800mA / 1mA                                  | 10-3000mA / 10mA |
| Output Power / Inc.   | 150W / 1W     | 300W / 1W                                      | 300W / 1W        |
| Output Pairs          | 5             | 5                                              | 5                |
| Output Type           | - - - - -     | Constant voltage / Current / Power             | - - - - -        |
| Program               | - - - - -     | Pre setting: Up to 6-step, 30 programmed files | - - - - -        |
| Timer                 | - - - - -     | Constant mode: 999 (min) with alarm            | - - - - -        |
| Programmable Mode:    | - - - - -     | 999 (min) with alarm                           | - - - - -        |
| Rated Voltage         | - - - - -     | 100 - 240V                                     | - - - - -        |